Buffer solution pH 6.88 AVS TITRINORM ready to use

Code number 83601

GENERAL INFORMATION

The ready to use buffer solutions are produced under specific conditions to avoid contamination and pollution of the solutions
For the preparation, all the raw materials used are AnalaR NORMAPUR Analytical reagent grade :

- Potassium di hydrogénophosphate
- Di Sodium hydrogenophosphate

SPECIFICATIONS

pH = 6,88 +/- 0,02 units of pH at 20 ℃
The real value at 20 ℃ is really indicated on the label

Variation of the pH following the temperature:

Temperature °C	0	10	15	20	25	30	40	50	60	70	80
pH	6,98	6,95	6,92	6,88	6,86	6,86	6,84	6,84	6,84	6,84	6,82

TRACEABILITY

The buffer pH 6,88 is traceable to SRM from NIST

SHELF LIFE

24 months

USE IN LABORATORY

Version : 12- 02 -2014

tel/tél +32(0)16 385 011
fax +32(0)16 385 385
info@be.vwr.com
www.vwr.com

Researchpark Haasrode 2020
Geldenaaksebaan 464 B-3001 Leuven
RPR/RPM Leuven
BTW/TVA BE 0403.593.343